

YE25R25, Aluminum Terminal Plug

By Burndy
Catalog # [YE25R25](#)

Terminal Plug for AL and ACSR, 1/0 AL,1/0 ACSR, 4.62 in Length, Tin Plated, Yellow, BG or 5/8-1 or 243 or 8A Index.



Application

for terminating aluminum or ACSR cable at cut-out, transformer and arrester.

General

Catalog Number	YE25R25
Color Code	Yellow
Die Index	K-5/8-1;243;BG;8A
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154151

Dimensions

Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.625 in
Dimension - P inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	24000

Product Assets

- [3D Models - YE25R25_MODEL-STEP](#)
- [3D Models - YE25R25_MODEL-PDF](#)
- [3D Models - YE25R25_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YE28R60_Lineart](#)
- [Sales Drawings - 50115710](#)
- [Specifications - YE25R25](#)