

Compression Terminal

By Burndy
Catalog # YE26LH88

Oil and water-tight terminal with shrouded, tin-plated, CU barrel and brazed plug Used for terminating insulated CU conductor at cutout or transformer, 8 IN L.



Application

Wire Termination

General

Connector Type	INLINE PIN
Die Index	241
Feature - Barrel Style	Shrouded
Finish Type	Tin-Plated
Insulation	Y
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYSEALPLUG™
Type	Shrouded Pin Terminals
UPC	781810023372
UPC 12 Digit	7818100233722

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.48 in
Dimension - Inside Diameter inch	0.73 in
Dimension - L Length Overall mm	289 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	11.38 in
Dimension - P inch	8.06 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Compact Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	4200

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SA055640-01](#)