



YE26LH89, Compression Terminal Plug, Oil/Water Tight with Shroud, 2/0 Str

By Burndy
Catalog # [YE26LH89](#)



Oil and water-tight terminal with shrouded, CU barrel and brazed plug Used for terminating insulated CU conductor at cutout or transformer, Conductor: 2/0 Str.

Application

Wire Termination

General

Catalog Number	YE26LH89
Connector Type	INLINE PIN
Die Index	241
Feature - Barrel Style	Shrouded
Finish Type	Tin-Plated
Insulation	Y
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYSEALPLUG™
Type	Shrouded Pin Terminals
UPC	781810023389
UPC 12 Digit	7818100233899

Dimensions

Dimension - B Length fraction	2-11/16 in
Dimension - B Length inch	2.67 in
Dimension - Inside Diameter inch	1.04 in
Dimension - L Length Overall mm	289 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	11.38 in
Dimension - P inch	8.06 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str	2/0 AWG
Compact Size	
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	4200

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YE27LH94_LineArt](#)
[Sales Drawings - SA055640-01](#)
[Specifications - YE26LH89](#)



A Hubbell brand