

YE26R60, Aluminum Terminal Plug

By Burndy
Catalog # [YE26R60](#)



Aluminium Hyplug Connector, 2/0 Str. Al 2/0 ACSR, 9-1/2 in L, Terminal Plug for Aluminum and ACSR.

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color

Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

General

Catalog Number	YE26R60
Color Code	Gray
Die Index	249;840;11A
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154205

Dimensions

Dimension - L Length Overall mm	241 mm
Dimension - Length Overall inch	9.50 in
Dimension - P inch	6 in

Conductor Related

Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	2/0 (6/1) Quail AWG
Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	4200

Product Assets

- [3D Models - YE26R60_MODEL-IGES](#)
- [3D Models - YE26R60_MODEL-PDF](#)
- [3D Models - YE26R60_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YE28R60_Lineart](#)
- [Sales Drawings - 50115710](#)
- [Specifications - YE26R60](#)