



YE28R60, Aluminum Terminal Plug

By Burndy
Catalog # [YE28R60](#)

Terminal Plug for AL and ACSR, 4/0 AL,4/0 ACSR, 9.5 in Length, Tin Plated, Pink, 840 or 249 or 11A Index.



Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

General

Color Code	Pink
Die Index	249;840;11A
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154304

Dimensions

Dimension - L Length Overall mm	241 mm
Dimension - Length Overall inch	9.50 in
Dimension - Outside Diameter inch	0.91 in
Dimension - P inch	6 in

Conductor Related

Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	4200

Product Assets

[3D Models - YE28R60_MODEL-PDF](#)
[3D Models - YE28R60_MODEL-STEP](#)
[3D Models - YE28R60_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50115710](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YE28R60-SPEC-EN | REV 8/2023