

YE2R25, Aluminum Terminal Plug

By Burndy
Catalog # [YE2R25](#)



Terminal Plug for AL and ACSR, #1-#2 AL, #2 ACSR, 4.62 in Length, Tin Plated, Orange, BG or 5/8-1 or 243 or 8A Index.

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color coded end caps

Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

General

Catalog Number	YE2R25
Color Code	Orange
Die Index	K-5/8-1;243;BG;8A
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154106
UPC 14 Digit GTIN	00781810154106

Dimensions

Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.625 in
Dimension - Outside Diameter inch	0.65 in
Dimension - P inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG;1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG

Certifications And Compliance

Buy America(n) Qualified	• TAA Compliant (All status valid till December 2024) • BABA Compliant (All status valid till December 2024)
Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	24000

Product Assets

[3D Models - YE2R25_MODEL-STEP](#)
[3D Models - YE2R25_MODEL-IGES](#)
[3D Models - YE2R25_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YE28R60_Lineart](#)
[Sales Drawings - 50115710](#)
[Specifications - YE2R25](#)