

YE361R60, Aluminum Terminal Plug

By Burndy
Catalog # [YE361R60](#)

Aluminium Hyplug Connector, 477, 500 Al 477 (18/1) ACSR, 10-5/8 in L, Terminal Plug for Aluminum and ACSR.



Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

General

Catalog Number	YE361R60
Color Code	Pink
Die Index	317;705;K-1-1/8-1
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154458
UPC 12 Digit	7818101544588

Dimensions

Dimension - L Length Overall mm	270 mm
Dimension - Length Overall inch	10.625 in
Dimension - P inch	6 in

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	477 kcmil;500 kcmil
Conductor - AL Str Size Range	477 kcmil-500 kcmil

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YE28R60_Lineart](#)
- [Sales Drawings - 50115710](#)
- [Specifications - YE361R60](#)