

YE4R25, Aluminum Pin Terminal

By Burndy
Catalog # [YE4R25](#)



Al Compression terminal, #4 #2 #3 AWG 7,1,7 str, 4.62"stud, Orange, BG or 243 index.

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color

Application

For Aluminium and ACSR

General

Catalog Number	YE4R25
Color Code	Orange
Die Index	K-5/8-1;243;BG;8A
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG,PIN TERMINALS
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154052

Dimensions

Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.62 in
Dimension - Outside Diameter inch	0.65 in
Dimension - P inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size	4 AWG;3 AWG
Conductor - AL Str Size Range	4 AWG-3 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	24000

Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YE28R60_Lineart](#)
[Sales Drawings - 50115710](#)
[Specifications - YE4R25](#)