



# Bare Ferrule For 4 AWG

By Burndy  
Catalog # [YF0420UIL](#)

Bare Ferrule For 4 AWG.



### Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- UL listed per UL486F requirements
- RoHS Compliant

### Application

For Use On Copper Conductor

### General

Connector Type	End Termination
EU RoHS Indicator	Yes
Insulation	N
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	621945623347

### Dimensions

Dimension - D inch	0.30 in
Dimension - D1 inch	0.29 in
Dimension - D2 inch	0.37 in
Dimension - Length Overall inch	0.79 in

### Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor Size	4 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	100
Minimum Pack Quantity	100

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50111874](#)



A proud member of the Hubbell Family.