



YF0815UIL, Bare Ferrule For 8 AWG

By Burndy
Catalog # [YF0815UIL](#)



Bare Ferrule For 8 AWG.

Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- UL listed per UL486F requirements
- RoHS Compliant

Application

For Use On Copper Conductor

General

Catalog Number	YF0815UIL
Connector Type	End Termination
EU RoHS Indicator	Yes
Insulation	N
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	621945620315

Dimensions

Dimension - D inch	0.19 in
Dimension - D1 inch	0.18 in
Dimension - D2 inch	0.23 in
Dimension - Length Overall inch	0.59 in

Conductor Related

Conductor - Copper Solid Size	8 AWG
Conductor - Copper Str Size	8 AWG
Conductor Size	8 AWG

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	250
Minimum Pack Quantity	250

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50111874](#)
[Specifications - YF0815UIL](#)



A Hubbell brand