


## YF1209UIL, Bare Ferrule For 12 AWG

By Burndy  
Catalog # [YF1209UIL](#)



Bare Ferrule For 12 AWG.

### Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- UL listed per UL486F requirements
- RoHS Compliant

### Application

For Use On Copper Conductor

### General

Catalog Number	YF1209UIL
Connector Type	End Termination
EU RoHS Indicator	Yes
Insulation	N
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	621945623231

### Dimensions

Dimension - D inch	0.13 in
Dimension - D1 inch	0.11 in
Dimension - D2 inch	0.16 in
Dimension - Length Overall inch	0.35 in

### Conductor Related

Conductor - Copper Solid Size	12 AWG
Conductor - Copper Str Size	12 AWG
Conductor Size	12 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50111874](#)  
[Specifications - YF1209UIL](#)