

# YF1808UIL, Bare Ferrule For 18 AWG

By Burndy  
Catalog # [YF1808UIL](#)



Bare Ferrule For 18 AWG.

**Features**

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- UL listed per UL486F requirements
- RoHS Compliant

**Application**

For Use On Copper Conductor

**General**

Catalog Number	YF1808UIL
Connector Type	End Termination
EU RoHS Indicator	Yes
Insulation	N
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	621945621558

**Dimensions**

Dimension - D inch	0.07 in
Dimension - D1 inch	0.06 in
Dimension - D2 inch	0.09 in
Dimension - Length Overall inch	0.31 in

**Conductor Related**

Conductor - Copper Solid Size	18 AWG
Conductor - Copper Str Size	18 AWG
Conductor Size	18 AWG

**Certifications And Compliance**

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

**Logistics**

Carton Quantity	1
Minimum Pack Quantity	1000

**Product Assets**

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50111874](#)  
[Specifications - YF1808UIL](#)