



Installation Ratchet Crimper for Bare and Covered Ferrules, #22 AWG - #10 AWG, Dieless wth Square Crimp Profile

By Burndy
Catalog # [YF2210FL](#)



Ratchet Crimper for Bare and Covered Ferrules, #22-10 AWG, Dieless.

Features

- Front load crimping position
- Dieless crimping without multiple grooves
- Square crimp profile
- Full cycle ratchet mechanism
- Ratchet release lever

Application

Crimping

General

Application - For Use On	Bare and Covered Ferrules
Die Type	Dieless
EU RoHS Indicator	Yes
Sub Brand	FERRULES
Tool Type	Ratchet Crimper for Ferrules
Type	Crimper
UPC	781810542644
UPC 12 Digit	7818105426444

Dimensions

Dimensions	7.75 in x 2.32 in x 1.00 in
Height	1.00 in
Length	7.75 in
Weight	0.82 lb
Width	2.32 in

Conductor Related

Crimping Ranges	Copper: #22 AWG - #10 AWG
-----------------	---------------------------

Certifications and Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Sales Drawings - 30025747](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YF2210FL-SPEC-EN | REV 10/2023