

# YF25040UIL, Bare Ferrule For 250 kcmil

By Burndy  
Catalog # [YF25040UIL](#)

Bare Ferrule For 250 kcmil.



## Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- RoHS Compliant

## Application

For Use On Copper Conductor

## General

Catalog Number	YF25040UIL
Connector Type	End Termination
EU RoHS Indicator	Yes
Insulation	N
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	621945623491

## Dimensions

Dimension - D inch	0.81 in
Dimension - D1 inch	0.77 in
Dimension - D2 inch	0.91 in
Dimension - Length Overall inch	1.57 in

## Conductor Related

Conductor - Copper Solid Size	250 kcmil
Conductor - Copper Str Size	250 kcmil
Conductor Size	250 KCMIL

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	11600

## Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50111874](#)  
[Specifications - YF25040UIL](#)