



Ratchet Ferrule Crimper, Side Load Capability with (3) Interchangeable Dies, Use with Bare and Covered UL Listed Ferrule Series, #26 AWG - 1/0 AWG.

By Burndy
Catalog # [YF261CSKIT](#)

Crimper for Bare and Covered Ferrules, (3) Dies, #26 AWG - 1/0 AWG, Side Load.

Features

-
-
-
-
-
-

Application

Crimping

General

Application - For Use On	Bare and Covered Ferrules
Catalog Number	YF261CSKIT
Tool Type	Ratchet Crimper for Ferrules
Type	Crimper
UPC	621945625938

Dimensions



Dimensions	10.00 in x 2.70 in x 0.90 in
Height	0.9 in
Length	10 in
Weight	1.25 lb
Width	2.7 in

Conductor Related

Crimping Ranges	Copper: #26 AWG - #1/0 AWG
-----------------	----------------------------

Logistics

Package Contents	Tool, YF2610D, YF864D, YF21D, torque key, plastic case
------------------	--

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - YF261CSKIT](#)
- [Video - BURNDY® cULus Listed Ferrules](#)