



YF3/025UIL - Old Version, Bare Ferrule For 3/0 AWG

By Burndy
Catalog # YF3/025UIL

Bare Ferrule For 3/0 AWG.

Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- RoHS Compliant

Application

For Use On Copper Conductor

General

Catalog Number	YF3/025UIL
Connector Type	End Termination
EU RoHS Indicator	Yes
Insulation	N
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	621945623460

Dimensions

Dimension - D inch	0.61 in
Dimension - D1 inch	0.58 in
Dimension - D2 inch	0.68 in



Dimension - Length Overall 0.98 in
inch

Conductor Related

Conductor - Copper Solid Size	3/0 AWG
Conductor - Copper Str Size	3/0 AWG
Conductor Size	3/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50149598](#)
[Specifications - YF3025UIL](#)



A Hubbell brand