

YF35040UIL, Bare Ferrule For 350 kcmil

By Burndy
Catalog # [YF35040UIL](#)

Bare Ferrule For 350 kcmil.

Application

For Use On Copper Conductor


General

Catalog Number	YF35040UIL
Connector Type	End Termination
EU RoHS Indicator	Yes
Insulation	N
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	FERRULES
Type	Bootlace Ferrule
UPC	621945623514

Dimensions

Dimension - D inch	0.84 in
Dimension - D1 inch	0.80 in
Dimension - D2 inch	0.94 in
Dimension - Length Overall inch	1.57 in

Conductor Related



Conductor - Copper Solid Size	350 kcmil
Conductor - Copper Str Size	350 kcmil
Conductor Size	350 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	11600

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50111874](#)
[Specifications - YF35040UIL](#)