



YGA25N Compression Grounding Lug, 1/0 AWG Cu, 1/2" Stud

By Burndy
Catalog # YGA25N



HYGROUND® Grounding Irreversible Compression Terminals: 1-Hole with Inspection Window; Accommodates: 1/0 AWG; 1/2" Stud.

General

Catalog Number	YGA25N
Color Code	Pink
Connector Type	Terminal
Die Index	12;348
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810226131
UPC 12 Digit	7818102261311

Dimensions

Dimension - B Length fraction	1-1/3 in
Dimension - B Length inch	1.35 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.06 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Strip Length inch	1-7/16

Conductor Related

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Carton Quantity	40
Minimum Pack Quantity	1
Pallet Quantity	30720

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50090245](#)
[Specifications - YGA25N](#)