



YGA262N Compression Grounding Lug, 2/0 AWG Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YGA262N](#)



HYGROUND® Grounding Irreversible Compression Terminals: 2-Hole with Inspection Window; Accommodates: 2/0 AWG; 1/2" Stud; 1-3/4" Spacing

Features

- Irreversible Compression Grounding Lug
- Inspection port to ensure proper cable insertion
- UL 467 Listed, acceptable for direct burial in earth or concrete
- Prefilled with PENETROX Oxide Inhibiting Compound and strip sealed
- 2 Stud Holes, 1/2" with 1-3/4" Spacing
- Die Index: 13

Application

For Grounding Applications And Direct Burial In Earth Or Concrete

General

Color Code	Black
Connector Type	Terminal
Die Index	13
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminals
UPC	781810220313
UPC 12 Digit	7818102203133

Dimensions

Dimension - B Length fraction	1-4/9 in
Dimension - B Length inch	1.45 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	126 mm
Dimension - Length Overall inch	4.97 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.56 in

Conductor Related

Conductor - Copper Str Size	2/0 Str.
Conductor - Copper Str Size Range	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	9600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YGA2N_LineArt](#)
[Sales Drawings - SD..082469-01](#)

inch

Dimension - Pad Width inch 0.81 in

Dimension - Strip Length inch 1-9/16

Dimension - Stud Size fraction 1/2

Dimension - Stud Size inch 1/2

Dimension - Width fraction 1/2 in

Dimension - Width inch 0.53 in



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YGA262N-SPEC-EN | REV 5/2024