



# YGA282N90 Compression Grounding Lug, 4/0 AWG Cu, 2-Hole, 1/2" Stud, 1-3/4" Stud, 90 Degree Pad

By Burndy  
Catalog # [YGA282N90](#)



HYLUG™ Copper Compression Terminal for Grounding; 2-Hole; 1/2" Stud; 1-3/4" Spacing; 90 Degree Pad; Long Barrel; Accommodates: 4/0 AWG.

## General

Color Code	Purple
Connector Type	Terminal
Die Index	15
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810267158
UPC 12 Digit	7818102671588

## Dimensions

Dimension - B Length fraction	1-3/5 in
Dimension - B Length inch	1.59 in
Dimension - Height fraction	2-2/5 in
Dimension - Height inch	2.39 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	131 mm
Dimension - Length Overall inch	5.17 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.02 in
Dimension - Strip Length inch	1-11/16
Physical Attribute - Tongue Angle	90 Degree

## Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YGA282N90-SPEC-EN | REV 5/2024