



YGA2C2TC38E2G1 Compression Grounding Lug

By Burndy
Catalog # YGA2C2TC38E2G1



Grounding Irreversible Compression Terminals.

General

Catalog Number	YGA2C2TC38E2G1
Color Code	Brown
Connector Type	Terminal
Die Index	10
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810109632
UPC 12 Digit	7818101096322

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size inch	0.38 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	93 mm
Dimension - Length Overall inch	3.66 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	3/8

Conductor Related

Conductor - Copper Solid Size	2 AWG
-------------------------------	-------

Conductor - Copper Solid Size Range	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor Type	<ul style="list-style-type: none">CU C Solid-SizeCU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL467UL 486A-486B
Standards - Industry Standards Met	UL467;UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD209500](#)
- [Specifications - YGA2C2TC38E2G1](#)