



## **YGA6C2N Compression Grounding Lug, #6 AWG Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing**

By Burndy  
Catalog # [YGA6C2N](#)

HYLUG™ Copper Compression Terminal for Grounding; 2-Hole; 1/2" Stud; 1-3/4" Spacing; Long Barrel; Accommodates: #6 AWG.



## Application

HYLUG ground terminal specially designed for grounding applications

## General

Catalog Number	YGA6C2N
Color Code	Blue
Connector Type	Terminal
Construction Material - Main	Copper
Die Index	7;374
EU RoHS Indicator	Contact Manufacturer
Material	Copper
Physical Attribute - Number of	2
Crimps Required	
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YGA-2N
UPC	781810091739
UPC 12 Digit	7818100917399

## Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.09 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	112 mm
Dimension - Length Overall inch	4.40 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Width fraction	2/5 in
Dimension - Width inch	0.41 in

## Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Str Size	6 Sol./6 Str.
Conductor - Copper Str Size Range	6 Sol / 6 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	24000

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YGA2N\\_LineArt](#)  
[Sales Drawings - SD..082469-01](#)  
[Specifications - YGA6C2N](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YGA6C2N-SPEC-EN | REV 8/2024