



YGA6C2TC38E2G1 Compression Grounding Lug

By Burndy
Catalog # [YGA6C2TC38E2G1](#)

Grounding Irreversible Compression Terminals.



General

Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810109656
UPC 12 Digit	7818101096566

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size inch	0.25 in
Dimension - Hole Size inch	0.49 in
Dimension - Hole Size mm	12 mm
Dimension - L Length Overall mm	87 mm
Dimension - Length Overall inch	3.42 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	3/8

Conductor Related

Conductor - Copper Solid Size	6
Conductor - Copper Solid Size Range	6
Conductor - Copper Str Size	6 Sol./6 Str.
Conductor - Copper Str Size Range	6 Sol / 6 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 467
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD209500](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YGA6C2TC38E2G1-SPEC-EN | REV 8/2023