



YGA8C2N Compression Grounding Lug

By Burndy
Catalog # YGA8C2N

HYLUG™ Copper Compression Terminal for Grounding; 2-Hole; 1/2" Stud; 1-3/4" Spacing; Long Barrel; Accommodates: #8 AWG.



General

Color Code	Red
Connector Type	Terminal
Die Index	49
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810102404
UPC 12 Digit	7818101024044

Dimensions

Dimension - B Length fraction	7/9 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.09 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Width fraction	1/3 in
Dimension - Width inch	0.31 in

Conductor Related

Conductor - Copper Solid Size	8 AWG
Conductor - Copper Solid Size Range	8 AWG
Conductor - Copper Str Size	8 Sol./8 Str.
Conductor - Copper Str Size Range	8 Sol./8 Str.
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	24000

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..082469-01](#)



A proud member of the Hubbell Family.

