



YGA8CTC10 Compression Grounding Lug, #8 AWG, #10 Stud

By Burndy
Catalog # [YGA8CTC10](#)



Grounding Irreversible Compression Terminals 8 Awg #10 bolt size.

General

Color Code	Red
Connector Type	Terminal
Die Index	49
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYGROUND®
Type	Terminals
UPC	781810247822
UPC 12 Digit	7818102478222

Dimensions

Dimension - B Length fraction	4/5 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.57 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	#10

Conductor Related

Conductor - Copper Solid Size	8
Conductor - Copper Solid Size Range	8
Conductor - Copper Str Size	8 Sol./8 Str.
Conductor - Copper Str Size Range	8 Sol / 8 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	<ul style="list-style-type: none">• UL 467• Direct Burial
Standards - Industry Standards Met	UL467;UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD209500](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YGA8CTC10-SPEC-EN | REV 5/2024