

YGC6C6 Compression C-Crimp Connector, #6 Sol/Str Run and Tap

By Burndy
Catalog # [YGC6C6](#)



COPPER CRIMPIT™ Compression C Connector, .62 in L, #6 Sol. #6 Sol. (Run), #6 Sol. #6 Sol. (Tap).

Features

- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ E2 oxide inhibiting compound

Application

For Direct Burial In Earth Or Concrete

General

Catalog Number	YGC6C6
Connector Type	Tap
Die Index	BG
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, CRIMPIT
Trade Name	CRIMPIT™
Type	Taps
UPC	781810102626
UPC 12 Digit	7818101026266

Dimensions

Dimension - Height fraction	19/25 in
Dimension - Height inch	0.76 in
Dimension - Height mm	19.3 mm
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in

Conductor Related

Conductor - Copper Solid Run	6 AWG
Conductor - Copper Solid Run Range	6 AWG

Conductor - Copper Solid Tap	6 AWG
Conductor - Copper Solid Tap Range	6 AWG
Conductor - Copper Str Run	6 AWG
Conductor - Copper Str Run Range	6 AWG
Conductor - Copper Str Tap	6 AWG
Conductor - Copper Str Tap Range	6 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	46400

Product Assets

[Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YGC_LineArt](#)
[Sales Drawings - SD..209501-01](#)
[Specifications - YGC6C6](#)