

## YGHA26NTN Compression Grounding Lug, 2/0 AWG Cu, 1-Hole, 1/2" Stud, Tin Plated

By Burndy  
Catalog # [YGHA26NTN](#)



HYLUG™ Copper Compression Terminal for Grounding; Heavy Duty; 1-Hole.

### General

Catalog Number	YGHA26NTN
Connector Type	Terminal
Die Index	15
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Terminals
UPC	781810346631
UPC 12 Digit	7818103466311

### Dimensions

Dimension - B Length fraction	39/47 in
Dimension - B Length inch	0.83 in
Dimension - D inch	1.27 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.63 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.71 in
Dimension - Pad Width inch	0.97 in
Dimension - Z (inch)	0.64 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL467;UL468A-468B;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	11600

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SD..211241-01](#)  
[Specifications - YGHA26NTN](#)