



YGHA29N Compression Grounding Lug

By Burndy
Catalog # [YGHA29N](#)

HYLUG™ Copper Compression Terminal for Grounding; Heavy Duty; 1-Hole.



*Representative Image

General

Connector Type	Terminal
Die Index	18
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810127070
UPC 12 Digit	7818101270700

Dimensions

Dimension - B Length fraction	1-9/50 in
Dimension - B Length inch	1.18 in
Dimension - D inch	1.27 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.18 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.28 in
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• UL468A-468B• IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	3840

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..211241-01](#)



A proud member of the Hubbell Family.