



YGHA2C2NTN Compression Grounding Lug, #2 AWG Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Tin Plated

By Burndy
Catalog # YGHA2C2NTN



Tin plated Heavy Duty Copper Compression Lug, 2 Hole with Inspection probe hole, 2 AWG, 1/2" Stud, 1-3/4" stud hole spacing, short barrel.

General

Connector Type	Terminal
Die Index - Element B	11
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Terminals
UPC	781810532447
UPC 12 Digit	7818105324477

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.21 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.50 in
Dimension - Pad Width inch	0.97 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-486B • IEEE 837
Standards - Industry Standards Met	UL467;UL 486A-486B;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	9800

Product Assets

- [3D Models - YGHA2C2NTN_MODEL-STEP](#)
- [3D Models - YGHA2C2NTN_MODEL-PDF](#)
- [3D Models - YGHA2C2NTN_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD..082472-01](#)



A proud member of the Hubbell Family.