

YGHA2CNTN Compression Grounding Lug, 2 AWG Cu, 1-Hole, 1/2" Stud, Tin Plated

By Burndy
Catalog # [YGHA2CNTN](#)



Tin Plated Heavy Duty Irreversible Compression Terminals.

General

Catalog Number	YGHA2CNTN
Connector Type	Terminal
Die Index - Element B	11
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Terminals
UPC	621945454743
UPC 12 Digit	6219454547433

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	1.27 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	2.46 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.50 in
Dimension - Pad Width inch	0.97 in
Dimension - Z (inch)	0.64 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	Yes
Standards - Industry Standards Met	UL467;UL468A-468B;IEEE 837
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	50
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..211241-01](#)
[Specifications - YGHA2CNTN](#)