



YGHA31N Compression Grounding Lug

By Burndy
Catalog # [YGHA31N](#)

HYLUG™ Copper Compression Terminal for Grounding; Heavy Duty; 1-Hole.



*Representative Image

General

Connector Type	Terminal
Die Index	20
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810209936
UPC 12 Digit	7818102099366

Dimensions

Dimension - B Length fraction	1-9/50 in
Dimension - B Length inch	1.18 in
Dimension - D inch	1.27 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.20 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.17 in
Dimension - Pad Width inch	1.62 in
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL467• UL 486A-486B• IEEE 837
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• UL 486A-486B• IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	20
Pallet Quantity	2900

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..211241-01](#)



A proud member of the Hubbell Family.

