



YGHA362N Compression Grounding Lug

By Burndy
Catalog # [YGHA362N](#)



HYLUG™ Copper Compression Terminal for Grounding; Heavy Duty; 2-Hole.

General

Connector Type	Terminal
Die Index	576
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810340356
UPC 12 Digit	7818103403566

Dimensions

Dimension - B Length fraction	1-19/50 in
Dimension - B Length inch	1.38 in
Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	139 mm
Dimension - Length Overall inch	5.48 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.55 in
Dimension - Pad Width inch	2.10 in
Dimension - Z inch	0.62 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	600 kcmil
Conductor - Copper Str Size Range	600 kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	IEEE 837
Standards - Industry Standards Met	IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	1044

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..082472-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YGHA362N-SPEC-EN | REV 8/2023