



YGHC26C2TN Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHC26C2TN](#)



Copper Compression Ground Connector; .75 IN L; 1-2/0 Str. (Run); #6 Sol.-#2 Str. (Tap).

General

Catalog Number	YGHC26C2TN
Connector Type	Tap
Die Index	O
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810167298
UPC 12 Digit	7818101672988

Dimensions

Dimension - Height fraction	1-25/61 in
Dimension - Height inch	1.41 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in

Conductor Related

Conductor - Copper Solid Tap Range	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Tap Range	6 AWG-1 AWG
Conductor - Copper Str Run Range	1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	1 AWG-2/0 AWG
Conductor - Copper Str Tap Range	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	7 AWG-2 AWG
Conductor - Rod Run Range	3/8 in
Conductor - Rod Run Range	3/8 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	UL467;IEEE 837;UL468A-468B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	14800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD086223-01](#)
[Specifications - YGHC26C2TN](#)



A Hubbell brand