



YGHC29C29NP Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHC29C29NP](#)

Copper Compression Ground Connector; 3/0 Str.-250 kcmil (Run & Tap); 997 Index, NO Penetrox™.

Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete

General

Catalog Number	YGHC29C29NP
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYTAP™
Type	Taps
UPC	781810568903
UPC 14 Digit GTIN	00781810568903

Dimensions

Dimension - Height mm	0 mm
Dimension - L Length Overall mm	997 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL Listed to UL 467• CSA Certified to C22.2 No.41
Standards - Industry Standards Met	UL467;IEEE 837;UL468A-468B
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	125
Minimum Pack Quantity	1
Pallet Quantity	6125

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD086223-01](#)
- [Specifications - YGHC29C29NP](#)



A Hubbell brand