



# YGHC34C26TN Compression Grounding C-TAP Connector

By Burndy  
Catalog # [YGHC34C26TN](#)



Cu Compression Ground Tap Connector, .88 IN L, 300-500 Kcmil (Run), # 6 Sol. To 2/0 str (Tap), Tin Plated.

## General

Catalog Number	YGHC34C26TN
Connector Type	Tap
Die Index	1011
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810327937
UPC 12 Digit	7818103279377

## Dimensions

Dimension - Height fraction	2-21/50 in
Dimension - Height inch	2.42 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

## Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-3/0 AWG
Conductor - Copper Str Run	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	300 kcmil-500 kcmil
Conductor - Copper Str Tap	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	7 AWG-2/0 AWG
Conductor - Rod Run	3/4 in
Conductor - Rod Run Range	3/4 in

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	UL467;IEEE 837;UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	5920

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD086223-01](#)
- [Specifications - YGHC34C26TN](#)



A Hubbell brand