



YGHC34C29TN Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHC34C29TN](#)



Cu Compression Ground Tap Connector, .88 IN L, 300-500 Kcmil (Run), 3/0 Str. - 250 Kcmil (Tap), Tin Plated.

General

Catalog Number	YGHC34C29TN
Connector Type	Tap
Die Index	1011
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810110867
UPC 12 Digit	7818101108677

Dimensions

Dimension - Height fraction	2-2/3 in
Dimension - Height inch	2.67 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Run	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	300 kcmil-500 kcmil
Conductor - Copper Str Tap	3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	3/0-250

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	UL467;IEEE 837;UL468A-468B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	2960

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD086223-01](#)
- [Specifications - YGHC34C29TN](#)