



## YGHC34C34 Compression Grounding C-TAP Connector

By Burndy  
Catalog # [YGHC34C34](#)



Copper Compression C Connector, 300-500 kcmil (Run & Tap).

### Application

For Direct Burial Cables

### General

Catalog Number	YGHC34C34
Connector Type	Tap
Die Index	1011
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810221082
UPC 12 Digit	7818102210822

### Dimensions

Dimension - B Length inch	1.10 in
Dimension - Height fraction	2-81/89 in
Dimension - Height inch	2.91 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.10 in

### Conductor Related

Conductor - Copper Str Run	300;350;400;450;500
Conductor - Copper Str Run Range	300-500
Conductor - Copper Str Tap	300;350;400;450;500
Conductor - Copper Str Tap Range	300-500

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	UL467;IEEE 837;UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	2960

### Product Assets

[3D Models - YGHC34C34\\_MODEL-IGES](#)  
[3D Models - YGHC34C34\\_MODEL-PDF](#)  
[3D Models - YGHC34C34\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YGHC\\_LineArt](#)  
[Sales Drawings - SD086223-01](#)



A Hubbell brand