



# YGHP29C26 Figure 6 Compression Grounding Connector, 1/0 Str-250 kcmil, 1/2"-5/8" Rod Run, 1/0-2/0 Str Tap

By Burndy  
Catalog # YGHP29C26



Cu Compression Ground Rod Connector, 1/0 Str - 2/0 str, 1/2" - 5/8" Rod Dia.

## Application

For Direct Burial In Earth And Concrete

## General

Catalog Number	YGHP29C26
Connector Type	Tap
Die Index	997
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810220931
UPC 12 Digit	7818102209311

## Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in

## Conductor Related

Conductor - Copper Str Run	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Run Range	1/0 -250 kcmil
Conductor - Copper Str Tap	1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	1/0 -2/0 AWG
Conductor - Rebar Run	3 ;4
Conductor - Rebar Run Range	3 -4
Conductor - Rod Run	1/2 in;5/8 in
Conductor - Rod Run Range	1/2 in-5/8 in

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	7350

## Product Assets

[3D Models - YGHP29C26\\_MODEL-PDF](#)  
[3D Models - YGHP29C26\\_MODEL-IGES](#)  
[3D Models - YGHP29C26\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section E1 - Compression Grounding](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YGHPC\\_Lineart](#)  
[Sales Drawings - sd082473-01](#)  
[Sell Sheets - HYTAP™ Figure 6 Connector, HYGROUND® Mechanical Grounding](#)



