

YGHP29C29TN Figure 6 Compression Grounding Connector, 1/0 Str-250 kcmil, 1/2"-5/8" Rod, 3/4"-1/2" Rebar Run; 3/0 Str-250 kcmil Tap

By Burndy
Catalog # [YGHP29C29TN](#)



HYTAP™ Figure 6 Tap HYGROUND® Compression Connector or Tap Splice Connector; Accommodates: Run: 1/0 Str. - 250 kcmil; 1/2" - 5/8" Rod; Tap: 3/0 Str. - 250 kcmil.; Rebar Run: 3/8" - 1/2" Rebar; Tap 3/0 Str. - 250 kcmil.

General

Catalog Number	YGHP29C29TN
Connector Type	Tap
Die Index	997
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810171592
UPC 12 Digit	7818101715922

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Height mm	0 mm
Dimension - Length Overall inch	2.09 in

Conductor Related

Conductor - Copper Str Run	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Run Range	1/0 -250 kcmil
Conductor - Copper Str Tap	3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	3/0 AWG-250 kcmil

Conductor - Rebar Run	3 ;4
Conductor - Rebar Run Range	3 -4
Conductor - Rod Run	1/2 in;5/8 in
Conductor - Rod Run Range	1/2 in-5/8 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	9800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd082473-01](#)
[Specifications - YGHP29C29TN](#)