



YGHP34C29TN Figure 6 Compression Grounding Connector, 250-500 kcmil, 5/8"-3/4" Rod, 5/8"-3/4" Rebar Run; 3/0 Str-250 kcmil Tap, Tin Plated

By Burndy

Catalog # [YGHP34C29TN](#)



HYTAP™ Figure 6 Tap HYGROUND® Compression Connector or Tap Splice Connector; Accommodates: Run: 250 - 500 kcmil; 5/8" - 3/4" Rod; Tap: 3/0 Str. - 250 kcmil.; Rebar Run: 5/8" - 3/4" Rebar; Tap 3/0 Str. - 250 kcmil.

Features

- Irreversible compression ground tap can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

General

Catalog Number	YGHP34C29TN
Connector Type	Tap
Die Index	998
Material	Copper
Physical Attribute - Number of	1
Crimps Required	
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAP™
Type	Taps
UPC	781810203958
UPC 14 Digit GTIN	00781810203958

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Height mm	0 mm
Dimension - Length Overall inch	2.58 in

Conductor Related

Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250 kcmil-500 kcmil

Conductor - Copper Str Tap	3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	3/0-250
Conductor - Rebar Run	5 ;6
Conductor - Rebar Run Range	5 -6
Conductor - Rod Run	5/8 in;3/4 in
Conductor - Rod Run Range	5/8 in-3/4 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	5920

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd082473-01](#)
[Specifications - YGHP34C29TN](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YGHP34C29TN-SPEC-EN | REV 3/2025