



YGHP58C2W2 Figure 6 Compression Grounding Connector, 1/2"-5/8" Rod Run, #6- #2 Sol Tap

By Burndy
Catalog # YGHP58C2W2



High Conductivity Cu Compression Ground Tap Connector,
1/2" - 5/8" Rod Dia, #6 - #2 Sol(Tap).

Application

For Ground Rod, Direct Burial In Earth And Concrete

General

Catalog Number	YGHP58C2W2
Connector Type	Tap
Die Index	997
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810002186
UPC 12 Digit	7818100021866

Dimensions

Dimension - B Length fraction	1-9/10 in
Dimension - B Length inch	1.90 in
Dimension - Height inch	1.90 in
Dimension - Pad Width inch	0.75 in
Dimension - Width inch	0.94 in
Dimension - Width mm	24 mm

Conductor Related

Conductor - Copper Solid Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Run Range	6 AWG-2 AWG
Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Tap Range	6 AWG-2 AWG
Conductor - Rod Tap	1/2 in;5/8 in
Conductor - Rod Tap Range	1/2 in-5/8 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	8700

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_yghpc2la](#)
[Sales Drawings - SE207006-01_A](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YGHP58C2W2-SPEC-EN | REV 6/2024