

## YGHR26C58TN Figure 8 Compression Ground Rod Connector

By Burndy  
Catalog # [YGHR26C58TN](#)



HYTAIL™ Ground Rod Figure 8 Compression Tap Connector.

### General

Catalog Number	YGHR26C58TN
Connector Type	Tap
Die Index	998;1012
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAIL™
Type	Taps
UPC	781810226117
UPC 12 Digit	7818102261177

### Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	5/8
Dimension - Height fraction	1-32/33 in
Dimension - Height inch	1.97 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

### Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	2 AWG - 2/0 AWG
Conductor - Rod Size	5/8 in
Conductor - Rod Size Range	5/8 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size A</li> <li>• Rod-Size B</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul>
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	20
Minimum Pack Quantity	15
Pallet Quantity	4640

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - sd..088266-01](#)  
[Specifications - YGHR26C58TN](#)