



YGHR34C58TN Figure 8 Compression Ground Rod Connector

By Burndy
Catalog # [YGHR34C58TN](#)



HYTAIL™ Ground Rod Figure 8 Compression Tap Connector.

General

Connector Type	Tap
Die Index	998;1012
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAIL™
Type	Taps
UPC	621945150638
UPC 12 Digit	6219451506388

Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	5/8
Dimension - Height fraction	2-7/50 in
Dimension - Height inch	2.14 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Rod Size	5/8 in
Conductor - Rod Size Range	5/8 in
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size A• Rod-Size B

Certifications And Compliance

Certification - CSA Approved	[Delete]
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	<ul style="list-style-type: none">• UL467• IEEE 837
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - YGHR34C58TN_MODEL-STEP](#)
[3D Models - YGHR34C58TN_MODEL-IGES](#)
[3D Models - YGHR34C58TN_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YGHR34C58TN-SPEC-EN | REV 5/2024