



YGHS25 Compression Grounding Splice

By Burndy
Catalog # YGHS25

HYGROUND® Grounding Irreversible Compression Splice;
Heavy Duty; Accommodates: 1/0 AWG; 1.89" Length.



Application

For Direct Burial In Earth Or Concrete

General

| | |
|--|---------------|
| Connector Type | Splice |
| Die Index | 14 |
| EU RoHS Indicator | Yes |
| Material | Copper |
| Physical Attribute - Number of Crimps Required | 1 |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | HYLINK |
| Trade Name | HYLINK™ |
| Type | Splices |
| UPC | 781810220597 |
| UPC 12 Digit | 7818102205977 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length fraction | 5/6 in |
| Dimension - B Length inch | 0.83 in |
| Dimension - L Length Overall mm | 48 mm |
| Dimension - Length Overall inch | 1.89 in |
| Dimension - Outside Diameter inch | 0.63 in |

Conductor Related

| | |
|-----------------------------------|---------|
| Conductor - Copper Str Size | 1/0 AWG |
| Conductor - Copper Str Size Range | 1/0 AWG |

Certifications and Compliance

| | |
|---|---|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | <ul style="list-style-type: none">UL467UL 486A-486BIEEE 837 |
| Standards - Industry Standards Met | <ul style="list-style-type: none">UL467UL 486A-486BIEEE 837 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 9600 |

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd082513-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YGHS25-SPEC-EN | REV 8/2023