



YGHS28 Compression Grounding Splice, 4/0 AWG Cu

By Burndy
Catalog # [YGHS28](#)

HYGROUND® Grounding Irreversible Compression Splice;
Heavy Duty; Accommodates: 4/0 AWG; 2.59" Length



Application

For Direct Burial In Earth Or Concrete

General

Connector Type	Splice
Die Index	17
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splices
UPC	781810220474
UPC 12 Digit	7818102204744

Dimensions

Dimension - B Length fraction	1-1/6 in
Dimension - B Length inch	1.18 in
Dimension - L Length Overall mm	66 mm
Dimension - Length Overall inch	2.59 in
Dimension - Outside Diameter inch	0.89 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL467UL 486A-486BIEEE 837
Standards - Industry Standards Met	UL467;UL 486A-486B;IEEE 837
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	5760

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YGHS_LineArt](#)
[Sales Drawings - sd082513-01](#)



A proud member of the Hubbell Family.