



YGHS34TN Compression Grounding Splice, 500 kcmil Cu, Tin Plated

By Burndy
Catalog # [YGHS34TN](#)



HYGROUND® Grounding Irreversible Compression Splice; Heavy Duty; Accommodates: 500 kcmil; Tin Plated.

General

Catalog Number	YGHS34TN
Connector Type	Terminal
Die Index	22
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
Type	Splices
UPC	781810110713
UPC 12 Digit	7818101107133

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.48 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in
Dimension - Outside Diameter inch	1.24 in

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL467UL 486A-486BIEEE 837
Standards - Industry Standards Met	UL467;UL 486A-486B;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - YGHS34TN](#)



A Hubbell brand