




YGIBS284002N Structural Steel Compression Grounding Connector

By Burndy
Catalog # [YGIBS284002N](#)



Copper Compression Connector, Cable to Steel, 2 AWG - 4/0 AWG, Angled Flange, 0.338" - 0.400" Thickness, 2 holes, 1/2" Stud.

Application

For Direct Burial Cables

General

Connector Type	Tap
EU RoHS Indicator	Yes
I Beam Style	Standard Beam (Flange Angled)
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, GROUNDLINK
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810034965
UPC 12 Digit	7818100349655

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - I Beam Thickness Range inch	0.313;0.325;0.375;0.350
Dimension - I Beam Thickness inch	0.338" - 0.400"
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	6
Pallet Quantity	594

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd208416-03](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YGIBS284002N-SPEC-EN | REV 8/2023