




# YGIBS286132N Structural Steel Compression Grounding Connector

By Burndy  
Catalog # YGIBS286132N



GROUNDLINK™ Connector for Structural Steel Angled or Parallel Beam; Accommodates: #2 - 4/0 AWG; 3" Length.

## Application

For Direct Burial Cables

## General

Connector Type	Tap
EU RoHS Indicator	Yes
I Beam Style	Standard Beam (Flange Angled)
Material	Copper
Physical Attribute - Number of Tapped Holes	2
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, GROUNDLINK
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810039328
UPC 12 Digit	7818100393288

## Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - I Beam Thickness Range inch	0.501;0.525;0.550;0.562
Dimension - I Beam Thickness inch	0.550" - 0.613"
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in

## Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	1782

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YGIBS283382N\\_LineArt](#)  
[Sales Drawings - SD208416-04\\_B](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YGIBS286132N-SPEC-EN | REV 5/2024