




YGIBS344002N Structural Steel Compression Grounding Connector

By Burndy
Catalog # YGIBS344002N



I-Beam Connector for Copper Cable, 2 AWG - 500 kcmil.

General

Catalog Number	YGIBS344002N
Connector Type	Tap
I Beam Style	Standard Beam (Flange Angled)
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810034972
UPC 12 Digit	7818100349722

Dimensions

Dimension - B Length fraction	6 in
Dimension - B Length inch	6.00 in
Dimension - I Beam Thickness Range inch	0.313;0.325;0.375;0.350
Dimension - I Beam Thickness inch	0.338" - 0.400"
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in

Conductor Related

Conductor - Copper Str Size Range	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size	250 kcmil-500 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	348

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YGIBS283382N_LineArt](#)
[Sales Drawings - sd208416-03](#)
[Specifications - YGIBS344002N](#)