



# YGS25 Compression Grounding Splice, 1/0 AWG Cu

By Burndy  
Catalog # YGS25



HYGROUND® Grounding Irreversible Compression Splice;  
Accommodates: 1/0 Str.; 2.97" Length.

## General

Connector Type	Splice
Die Index	12
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLINK™
Type	Splices
UPC	781810220603
UPC 12 Digit	7818102206033

## Dimensions

Dimension - B Length fraction	1-1/3 in
Dimension - B Length inch	1.35 in
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.97 in
Dimension - Outside Diameter inch	0.51 in

## Conductor Related

Conductor - Copper Solid Size	1/0
Conductor - Copper Solid Size Range	1/0
Conductor - Copper Str Size	1/0 Sol./Str.
Conductor - Copper Str Size Range	1/0 Sol./Str.
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>UL467</li><li>UL 486A-486B</li></ul>
Standards - Industry Standards Met	UL 486A-486B;UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	9600

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YGS\\_LineArt](#)  
[Sales Drawings - SD..082514-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YGS25-SPEC-EN | REV 5/2024